

DATA SHEET

BDT21 – SOLID FRONT PRESSURE GAUGE

Badotherm pressure gauge model BDT21 is the soild front, safety pattern gauges according to the operational safety requirements of AMSE B40.100 and ANSI B 40.1.1. The BDT21 stainless steel safety gauge with phenolic casing has a solid front baffle wall and a full blow-out back. This pressure gauge is typically used for applications in the chemical, petro-chemical, and oil & gas industry or anywhere where safety comes first. These gauges are designed to withstand the severest of operating conditions created by the ambient environment and the process medium.



DESIGN INFORMATION DESIGN NORM SAFETY DESIGNATION **INGRESS PROTECTION** ASME B40.100 S3 as per EN837-2 IP67 per IEC 60529 STANDARD MODEL MATERIAL SPECIFICATIONS **PROCESS CONNECTION** TUBE CASE Bezel AISI316(L) AISI316 black ASA+PC black ASA+PC MOVEMENT WINDOW POINTER DIAL stainless steel laminated safety glass aluminium, black aluminium, white with black markings **TECHNICAL SPECIFICATIONS** 125 mm Connection 1/2" BSP/NPT Minimum range -1 bar Maximum range 1600 bar Accuracy 0.5% FSV adjustable slotted Pointer Mounting variations A/C/D Free zero Internal limit stop Min/Max **Connection construction** screwed Solid front, full blow out on the back Compensation plug material NBR Window gasket NBR PED (CE marking >200 bar) **SPECIAL EXECUTIONS** BDT21-M tube and socket Monel 400 **OPTIONS** 14/ . . . م مام · -+

WINDOW	polycarbonate
PROCESS CONNECTION	METRIC or BSPT in various sizes
RESTRICTOR SCREW	AISI316(L)
POINTER	micro adjustable
FILLING	BPF01 (glycerine), BPF02 (silicon)
FILLING KIT	compensation bellow, o-ring for front case seal, and mounting screws for rear cover
CLEANING	for oxygen service, or oil and grease free (in case of filling use BPF05)
CALIBRATION CERTIFICATES	5 points (rising and falling)
Atex	EX II 2 GD c (ATEX 94/9/EC)
Accessories	please check for matching accessories such as siphons (BDT42), snubbers (BDT45), swivel gauges (BDT47), overpressure protectors (BDT49), diaphragm seals and instrument needle valves and manifolds



DATA SHEET

BDT21 – SOLID FRONT PRESSURE GAUGE

PRESSURE DETAILS

WORKING PRESSURE

	125 mm				
steady	full scale value				
fluctuating	0.9 x full scale value				
short time	1.3 x full scale value				

TEMPERATURE DETAILS

FILLING FLUID				WINDOW			GASKETS		
			ambient	process			ambient		ambien
-	without		-40°C to 90°C	200°C	safe	ety glass	<200°C	window NBR	<100°C
BPF01	glycerine	1000 Cst	-20°C to 65°C	90°C	poly	carbonate	<120°C	fill plug NBR	<100°C
BPF02	silicone	1000 Cst	-40°C to 65°C	90°C				fill plug HNBR	<150°C


TEMPERATURE EFFECT

The variation of indication caused by the effect of temperature shall not exceed: ± 0.04 x (ambient temperature – reference temperature)% of the span

MOUNTING VARIATIONS

- type A bottom connection, direct mounting
- type C bottom connection, surface mounting (flange material in same material as casing and bezel)
- type D back connection, direct mounting

DRAWINGS



DIMENSIONS

ns	d	dl	L	Н	h	d2	d3	d4	weight
4½"	148	129	86	180	130	148	137	6	0.80 kg

All dimensions in mm



Holland – United Kingdom – Romania – India – Thailand – Dubai

To our knowledge, the information contained herein is accurate as of the date of this document. However neither Badotherm, nor its affiliates makes any warranty, express or limited, or accepts any liability in connection with this information or its use. This information is for technical skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other product. The user alone finally determines suitability of any information or material in contemplated use, the manner of use and whether any patents are infringed. This information gives typical properties only.

Badotherm reserves the right to make changes to the specifications and materials without prior notice. The latest version of the datasheet can be found on www.badotherm.com.

 $\ensuremath{\mathbb{C}}$ 2001 Badotherm, all rights reserved. Trademarks and/or other products referenced herein are either trademarks or registered trademarks of Badotherm.

modified 27-02-2013